



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP54841H0ECO 54W T5 45.2" 4100K 82 Cri Mini Bi-Pin Flour Lamp

Sylvania-Ledvance

Catalog Number	FP54841H0ECO
Manufacturer	Sylvania-Ledvance
Description	54W, T5 Pentron High Output (Ho) Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.2700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Miniature Bipin
beam angle	Universal
Lamp Type	PROGRAMMED RAPID START
lumens	4450 Initial Lumens at 25 Degrees C
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	54

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100

Descriptions

Description	54W T5 45.2" 4100K 82 CRI MINI BI-PIN FLOUR LAMP
extra long description	SYL FP54/841/HO/ECO/20906 FP54841HO
Long Description	54W, T5 PENTRON high output (HO) fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209062
Manufacturers Part Number	FP54/841/HO/ECO/20906
UPC	046135209062

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	40
Weight Per each	0.27



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

ANSI C78.81 - 2001
