



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP54865H0ECO Fluor Lamp

Sylvania-Ledvance

Catalog Number	FP54865H0ECO
Manufacturer	Sylvania-Ledvance
Description	54W, T5 Pentron High Output (Ho) Fluorescent Lamp, 6500K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.2697 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	30000
Base	Miniature Bipin
lumens	4050 Initial Lumens at 25 Degrees C
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	54

Material, Color, and Finish

color rendering index (cri)	85
color temperature	6500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.625
----------	-------

Descriptions

Description	FLUOR LAMP
extra long description	SYL FP54/865/HO/ECO/20862 FP54865HO
Long Description	54W, T5 PENTRON high output (HO) fluorescent lamp, 6500K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC
Product Type	FP54865HOECO 40/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135208621
Manufacturers Part Number	FP54/865/HO/ECO/20862
UPC	046135208621

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	40
Weight Per each	0.2697

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------