



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FS1408HD 8' Fiberglass Stepladder Iaa

Louisville Ladder

Catalog Number	FS1408HD
Manufacturer	Louisville Ladder
Description	Louisville Ladder, Fiberglass Material, 375 LB Load Rating, 52-3/4 In Base Spread, 25-9/16 In Base Width, 91.475 In (Open Height);97.727 In (Closed Height) Overall Height, 3 In Rung Width, 3 In Step Depth, 7 Steps, 29 LB
Weight per unit	28.1 (lbs/each)
Product Category	Hand Tools - Ladders

Features

Load Capacity	375 W
---------------	-------

Descriptions

Description	8' FIBERGLASS STEPLADDER IAA
Special Features	Features: Protop - Versatile And Durable; Da Boot For Slip Resistant Footing; Inside Spreader Braces; Riveted Step Construction With Gussets; Wide Back Braces; A Non- Conductive Structural Molded Top With Hardware Tray, Paint Can Holder, Handyman's Tool Slots, Pipe Holder, Curved Front Of Top Provides Leg Comfort And Convenient Magnet To Secure Small Steel Parts; Series: FS1400HD; Actual Cubic Ft: 8.700 CU-FT; Approx. Spread: 52-3/4 IN

Manufacturer Information

Brand	Louisville
GTIN	00728865086655
sub brand	BRUTE
UPC	728865086655

Taxonomies, Classifications, and Categories

Category Description	LADDERS
Type	Type IAA

Packaging

Carton	1
Weight Per each	28.0869

Uses, Certifications, and Standards

standard	CSA, ANSI A14.5, OSHA
----------	-----------------------