



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FT18DL835RSECO 18W CFL 4-Pin 35K 1250LM *Sylvania-Ledvance*

Catalog Number	FT18DL835RSECO
Manufacturer	Sylvania-Ledvance
Description	Dulux 18W Long Compact Fluorescent Lamp With 4 Pin Base, 3500K Color Temperature, 82 Cri, Ecologic For Use On Magnetic, Electronic and Dimming Ballasts
Weight per unit	0.2100 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

amperage rating	Ballast Dependent
average life	20000
Ballast Type	Electronic and Dimming
Base	2G11
Lamp Type	DULUX L
lumens	1,250
Shape	T5
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Wattage	18

Material, Color, and Finish

color rendering index (cri)	82
color temperature	3500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.625
Length	10.5

Descriptions

Description	18W CFL 4-PIN 35K 1250LM
extra long description	SYL FT18DL/835/RS/ECO/20594 FT18DL8
Long Description	DULUX 18W long compact fluorescent lamp with 4 pin base, 3500K color temperature, 82 CRI, ECOLOGIC for use on magnetic, electronic and dimming ballasts
Product Type	FT18DL835RSECO 10/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135205941
Manufacturers Part Number	FT18DL/835/RS/ECO/20594
UPC	046135205941



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Compact Fluorescent

Packaging

Carton	1
Package	10
Weight Per each	0.21

Uses, Certifications, and Standards

Application	Commercial/Residential
standard	ANSI C78.901 - 2001