ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

FT40DL835RSEC0 40W 4 Pin Twin Tube Biax 2G11 3500K Compact Fluor

Sylvania-Ledvance

Catalog Number	FT40DL835RSEC0
Manufacturer	Sylvania-Ledvance
Description	Dulux 40W Long Compact Fluorescent Lamp With 4 Pin Base, 3500K Color Temperature, 82 Cri, Ecologic For Use On Magnetic, Electronic and Dimming Ballasts
Weight per unit	0.4100 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

amperage rating	Ballast Dependent
Ballast Type	Electronic and Dimming
Base	2G11
Lamp Type	DULUX L
lumens	3150
Shape	T5
total harmonic distortion	Ballast Dependent
Wattage	40

Material, Color, and Finish

color rendering index (cri)	80 - 89

Descriptions

Description	40W 4 PIN TWIN TUBE BIAX 2G11 3500K COMPACT FLUOR
extra long description	LDV FT40DL/835/RS/ECO/20585 FT40DL8
Long Description	DULUX 40W long compact fluorescent lamp with 4 pin base, 3500K color temperature, 82 CRI, ECOLOGIC for use on magnetic, electronic and dimming ballasts

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135205859
Manufacturers Part Number	FT40DL/835/RS/ECO/20585
UPC	046135205859

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Compact Fluorescent

Packaging

Carton	1
Package	10
Weight Per each	0.41

Uses, Certifications, and Standards

standard	ANSI C78.901 - 2001