

TYPE GAR
Ground Connector

For Copper Cable to Rod



High copper alloy ground connector for joining a range of cable, parallel or at right angles to rod or tube. Especially good for fence posts. High copper alloy cast body with DURIMUM™ U-bolts, nuts and lockwashers, permit entire connection to be buried in ground or concrete without danger of corrosion.



Catalog Number	Ground Rod		Conductor Range
	IPS	Rod	
GAR114C	1/4	1/2	8 sol. - 4 str.
GAR1126	1/4	1/2	4 sol. - 2/0 str.
GAR1129	1/4	1/2	2/0 sol. - 250 kcmil
GAR644C	3/8	5/8 - 3/4	8 sol. - 4 str.
GAR6426	3/8	5/8 - 3/4	4 sol. - 2/0 str.
GAR6429	3/8	5/8 - 3/4	2/0 sol. - 250 kcmil
GAR6434	3/8	5/8 - 3/4	300 - 500 kcmil
GAR144C	1/2 - 3/4	7/8 - 1	8 sol. - 4 str.
GAR1426	1/2 - 3/4	7/8 - 1	4 sol. - 2/0 str.
GAR1429	1/2 - 3/4	7/8 - 1	2/0 sol. - 250 kcmil
GAR1434	1/2 - 3/4	7/8 - 1	300 - 500 kcmil
GAR154C	1	1-1/8 - 1-1/4	8 sol. - 4 str.
GAR1526	1	1-1/8 - 1-1/4	4 sol. - 2/0 str.
GAR1529	1	1-1/8 - 1-1/4	2/0 sol. - 250 kcmil
GAR1534	1	1-1/8 - 1-1/4	300 - 500 kcmil
GAR164C	1-1/4	1-3/8 - 1-1/2	8 sol. - 4 str.
GAR1626	1-1/4	1-3/8 - 1-1/2	4 sol. - 2/0 str.
GAR1629	1-1/4	1-3/8 - 1-1/2	2/0 sol. - 250 kcmil
GAR1634	1-1/4	1-3/8 - 1-1/2	300 - 500 kcmil
GAR174C	1-1/2	1-5/8 - 1-7/8	8 sol. - 4 str.
GAR1726	1-1/2	1-5/8 - 1-7/8	4 sol. - 2/0 str.
GAR1729	1-1/2	1-5/8 - 1-7/8	2/0 sol. - 250 kcmil
GAR1734	1-1/2	1-5/8 - 1-7/8	300 - 500 kcmil
GAR184C	2	2 - 2-3/8	8 sol. - 4 str.
GAR1826	2	2 - 2-3/8	4 sol. - 2/0 str.
GAR1829	2	2 - 2-3/8	2/0 sol. - 250 kcmil
GAR1834	2	2-1/2 - 2-7/8	300 - 500 kcmil
GAR194C	2-1/2	2-1/2 - 2-7/8	8 sol. - 4 str.
GAR1926	2-1/2	2-1/2 - 2-7/8	4 sol. - 2/0 str.
GAR1929	2-1/2	2-1/2 - 2-7/8	2/0 sol. - 250 kcmil
GAR1934	2-1/2	2-1/2 - 2-7/8	300 - 500 kcmil
GAR204C	3	3 - 3-1/2	8 sol. - 4 str.
GAR2026	3	3 - 3-1/2	4 sol. - 2/0 str.
GAR2029	3	3 - 3-1/2	2/0 sol. - 250 kcmil
GAR2034	3	3 - 3-1/2	300 - 500 kcmil
GAR214C	3-1/2	3-1/2 - 4	8 sol. - 4 str.
GAR2126	3-1/2	3-1/2 - 4	4 sol. - 2/0 str.
GAR2129	3-1/2	3-1/2 - 4	2/0 sol. - 250 kcmil
GAR2134	3-1/2	3-1/2 - 4	300 - 500 kcmil
GAR224C	4	4 - 4-1/2	8 sol. - 4 str.
GAR2226	4	4 - 4-1/2	4 sol. - 2/0 str.
GAR2229	4	4 - 4-1/2	2/0 sol. - 250 kcmil

