



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GAR1834 500MCM Ground Conn

Burndy LLC

Catalog Number	GAR1834
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 300 - 500 Kcmil, 2" to 2-3/8" Rod, 2" Pipe, Bright Dipped.
Weight per unit	3.0 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
----------	--------

Descriptions

Description	500MCM GROUND CONN
extra long description	BUR GAR1834 300-500CU 2 IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 300 - 500 kcmil, 2" to 2-3/8" Rod, 2" Pipe, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Ground Rod Size: 2 - 2-3/8 IN, Tube (ips) Size: 2 IN, Installation Torque: 480 IN-LB, Width: 4-1/8 IN, Height: 5-1/4 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810235409
Manufacturers Part Number	GAR1834
UPC	781810235409

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GAR

Packaging

Carton	1
Weight Per each	3.0099



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod
Or Tube, Direct Burial Cable, Fence Post

standard

UL467