



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GBM34 500MCM Ground Conn

Burndy LLC

Catalog Number	GBM34
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 300 Kcmil - 500 Kcmil, 1/2" Stud.
Weight per unit	0.4800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	COPPER ALLOY
----------	--------------

Descriptions

Description	500MCM GROUND CONN
extra long description	BUR GBM34 300-500 CU BAR 1 PC GRD
Long Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 300 kcmil - 500 kcmil, 1/2" Stud.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable To 1/4 IN Thick Bar, Type GBM Clamps Cable Directly On Bar Surface, One-Wrench Installation, UL467 Listed, The High Copper Alloy Cast Body And DURIIUM Bolts, Nuts, And Lockwashers Make The GBM Suitable For Direct Burial In Concrete Or Ground, Installation Torque: 480 IN-LB, Width: 2-3/8 IN, Height: 2-1/4 IN, Bar Thickness: 1/4 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810231463
Manufacturers Part Number	GBM34
UPC	781810231463

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GBM

Packaging

Carton	1
Weight Per each	0.48

Uses, Certifications, and Standards

Application	For Copper Cable To Bar, Direct Burial Cable
standard	UL467