




**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GCL30  
 7818100794788  
 4 Sol-300 Kcmil GRD CLAMP  
 Active

**Web Use**  
 BURNDY Product Line



Dimensional	
Width (in)	1.50
Length (in)	2.21
Height (in)	2.00
Size (Hex) or Size (Bolt)	1/2
Size (Hex) or Size (Bolt) - in	0.50

General	
Product Description	Cast Copper Alloy Ground Clamp, 4 Str. - 300, Cable to Bar

Conductor(s)	
Bar Thickness (Range)	N/A
Copper Solid Size (Range)	4 AWG-4/0 AWG
Copper Stranded (Range)	4 Str-300 kcmil

Physical	
Installation Torque	480
Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Copper Alloy

Approvals / Certifications	
Rated for Direct Burial	Y
UL Listed	N
CSA Certified	N
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175