



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GE232MAXNULTRA 2LIGHT 4' Dual Voltage Ballast

Ge By Current Lamps

Catalog Number	GE232MAXNULTRA
Manufacturer	Ge By Current Lamps
Description	Ge Ultramax™, 60 HZ, Normal Ballast Factor, Instant Start, 9.5 In Length, 1.3 In Width, 1 In Height, 2 or 1 F32T8
Weight per unit	1.1 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

Ballast Factor	Normal
start type	Instant Start

Dimensions and Weight

Height	1
Length	9.5
Width	1.3

Descriptions

Description	2LIGHT 4' DUAL VOLTAGE BALLAST
extra long description	GEL GE232MAXPN/ULTRA 72266 ELECTRON
Long Description	GE UltraMax™, 60 Hz, Normal Ballast Factor, Instant Start, 9.5 IN Length, 1.3 IN Width, 1 IN Height, 2 or 1 F32T8
Product Type	72266 Electronic Ballast
Special Features	GE232MAXP-N/ULTRA (replaces GE232MAX-N/ULTRA) Designation

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168722667
Manufacturers Part Number	GE232MAXPN/ULTRA
UPC	043168722667

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Ballasts_Fluorescent_Electronic

Packaging

Carton	1
Weight Per each	1.1

Uses, Certifications, and Standards

Frequency Rating	60
------------------	----