



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GE260ISMVN Lamp T12 120-277V Ballast

Ge By Current Lamps

Catalog Number	GE260ISMVN
Manufacturer	Ge By Current Lamps
Description	Ge, Multi-Volt ProLine™, 50 HZ, Normal Ballast Factor, Instant Start, 9.5 In Length, 1.7 In Width, 1.18 In Height
Weight per unit	1.4 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

Ballast Factor	Normal
start type	Instant Start

Dimensions and Weight

Height	1.18
Length	9.5
Width	1.7

Descriptions

Description	LAMP T12 120-277V BALLAST
extra long description	GEL GE260IS-MV-N 74474 ELECTRONIC B
Long Description	GE, Multi-Volt ProLine™, 50 Hz, Normal Ballast Factor, Instant Start, 9.5 IN Length, 1.7 IN Width, 1.18 IN Height
Product Type	74474 Electronic Ballast
Special Features	GE260IS-MV-N Designation

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168744744
Manufacturers Part Number	GE260IS-MV-N
UPC	043168744744

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts_Fluorescent_Electronic

Packaging

Carton	1
Package	10
Weight Per each	1.39

Uses, Certifications, and Standards

Frequency Rating	50
------------------	----