

Eaton GFEP120

Catalog Number: GFEP120

Eaton BR GFCI circuit breaker, Industrial ground fault thermal-magnetic equipment protector, 20 A, 10 kAIC, Single-pole, 120 V, GFEP, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

General specifications



Product Name	Catalog Number
Eaton BR GFCI circuit breaker	GFEP120
UPC	Product Length/Depth
786676382052	3 in
Product Height	Product Width
1.25 in	4.75 in
Product Weight	Warranty
0.45 lb	Limited lifetime
Certifications	Catalog Notes
UL 489	Meets Federal Spec Classification W-C375

Product specifications

Type

Industrial ground fault thermal-magnetic equipment protector

Amperage Rating

20 A

Voltage rating

120 V

Trip Type

Common

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Interrupt rating

10 kAIC

Main circuit breaker

GFEP

Wire size

#14-4 AWG

Number of poles

Single-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - GFEP120](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)