



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFR5362SG 20A 125V Ind Tamper ST Gfci, Brown

Hubbell Wiring Devices

Catalog Number	GFR5362SG
Manufacturer	Hubbell Wiring Devices
Description	Power Protection Products, Receptacle, Gfci, Industrial Grade, Safetygrade Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown
Weight per unit	0.5500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired Terminal Screws
Material	Thermoplastic
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wattage	2,000
Wire Size	#14 AWG to #12 AWG

Material, Color, and Finish

Color	Brown
-------	-------

Dimensions and Weight

Size	Standard Sized
------	----------------

Descriptions

Description	20A 125V IND TAMPER ST GFCI, BROWN
extra long description	HCI GFR5362SG 20A/125V INDL. TAMPER
Long Description	Power Protection Products, Receptacle, GFCI, Industrial Grade, SafetyGrade Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown
Product Type	20A/125V Indl. Tamper ST Gfci, Brown
Special Features	Self Test Feature

Manufacturer Information

Brand	Hubbell Wiring Device-Kellems
GTIN	00783585440941
Manufacturers Part Number	GFR5362SG
sub brand	Straight Blade GFCI Receptacles
UPC	783585440941



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	DECORATOR DUPLEX

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.55

Uses, Certifications, and Standards

Application	Extra Heavy Duty with Self Test
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	NEMA WD1 and WD5, UL 498 and 943