



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFR8300SGR 20A 125V Ind HG Tamper ST Gfci, Red *Hubbell Wiring Devices*

Catalog Number	GFR8300SGR
Manufacturer	Hubbell Wiring Devices
Description	Power Protection Products, Receptacle, Gfci, Safety Grade Commercialhospital Grade, Led Indicator, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Red
Weight per unit	0.4000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired Terminal Screws
Material	Thermoplastic
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wattage	2,000
Wire Size	#14 AWG to #12 AWG

Material, Color, and Finish

Color	Red
-------	-----

Dimensions and Weight

Size	Standard Sized
------	----------------

Descriptions

Description	20A 125V IND HG TAMPER ST GFCI, RED
extra long description	HCI GFR8300SGR 20A/125V INDL. HG TA
Long Description	Power Protection Products, Receptacle, GFCI, Safety Grade CommercialHospital Grade, LED Indicator, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,Red
Product Type	20A/125V Indl. HG Tamper ST Gfci, Red
Special Features	Self-Testing, Tamper and Weather Resistant

Manufacturer Information

Brand	Hubbell Wiring Device-Kellems
GTIN	00783585441092
Manufacturers Part Number	GFR8300SGR
sub brand	Straight Blade GFCI Receptacles
UPC	783585441092



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	DUPLEX

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Hospital Grade GFCI Receptacles
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	NEMA WD1 and WD5, UL 498 and 943