



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GGC14 1-1/4X1/4 Fuse 250V 1/4A GGC

Mersen Fuses

Catalog Number	GGC14
Manufacturer	Mersen Fuses
Description	250V, Fast Acting, Glass 1/4" X 1 1/4" 250 Volts 0.25 Amps GGC Series.
Weight per unit	0.0050 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	0.25
connection	Ferrule
interrupt rating	0.2
Voltage Rating	250

Descriptions

Description	1-1/4X1/4 FUSE 250V 1/4A GGC
extra long description	FERRAZ GGC1/4 250V 1/4A 1-1/4X1/4 F
Long Description	250V, Fast Acting, Glass 1/4" x 1 1/4" 250 Volts 0.25 Amps GGC series.
Product Type	1-1/4X1/4 Fuse 250V 1/4A GGC
Special Features	Glass / Ceramic Body, 5mm x 20mm, Time-Delay, GSC-V fuses have 1-1/2" wire lead each end.

Manufacturer Information

Brand	Ferraz Shawmut
GTIN	00782001760571
Manufacturers Part Number	GGC1/4
UPC	782001760571

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	1/4 X 1-1/4

Packaging

Carton	1
Package	5
Weight Per each	0.005

Uses, Certifications, and Standards

Application	Electronic Circuits
Mounting	Clip
standard	UL/CSA Std. 248-14 1/10A - 10A, 250VAC UL listed, CSA certified 12A and 15A, 125VAC UL Listed, CSA certified 20A - 30A, 32VAC RoHS Compliant