



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **GHB2020 Type GHB BRKR 2P 20A 277/480VAC Max 125/250VDC Max** *Eaton Corp*

Catalog Number	GHB2020
Manufacturer	Eaton Corp
Description	Molded Case Circuit Breaker, 20 A, Non-Interchangeable Thermal Magnetic Tripping Mechanism, Bolt-On, 277/480 V Ac;125/250 V DC, G-Frame Frame, 50/60 HZ, 2.8 In Overall Height, 4.7 In Overall Length, 2.1 In Overall Width
Weight per unit	0.9500 (lbs/each)
Product Category	2 Pole

### **Features**

Current Rating	20 A
dimensions	2.6300 IN X 2.0000 IN X 4.0000 IN
frame	G
media	Yes
Poles	2

### **Descriptions**

Description	TYPE GHB BRKR 2P 20A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHB2020 GHB CB 2P 20A 277/480VA

### **Manufacturer Information**

Brand	Viton(R)
GTIN	00786679911204
UPC	786679911204

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker

### **Packaging**

Carton	1
Weight Per each	0.95

### **Uses, Certifications, and Standards**

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
standard	UL Listed,Federal Specifications Classification W-C375B