



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHB2025 Type GHB BRKR 2P 25A 277/480VAC Max 125/250VDC Max Eaton Corp

| | |
|------------------|---|
| Catalog Number | GHB2025 |
| Manufacturer | Eaton Corp |
| Description | Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 25 A, 480Y/277 Vac, 125/250 VDC, 50/60 HZ |
| Weight per unit | 2.0 (lbs/each) |
| Product Category | 2 Pole |

Features

| | |
|----------------|-----------------------------------|
| Current Rating | 25 A |
| dimensions | 2.6300 IN X 2.0000 IN X 3.0000 IN |
| media | Yes |
| Poles | 2 |
| Trip Type | Fixed thermal, fixed magnetic |
| Voltage Rating | 480Y/277 Vac, 125/250 Vdc |

Descriptions

| | |
|------------------------|---|
| Description | TYPE GHB BRKR 2P 25A 277/480VAC MAX 125/250VDC MAX |
| extra long description | ETN GHB2025 GHB CB 2P 25A 277/480VA |
| Features | Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A. |
| Long Description | Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 25 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz |
| Product Type | GHB CB 2P 25A 277/480VAC Max 125/250VDC |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786679172452 |
| Manufacturers Part Number | GHB2025 |
| UPC | 786679172452 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Molded case circuit breaker |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 2 |

Uses, Certifications, and Standards

| | |
|------------------|--|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other |
| Frequency Rating | 50/60 Hz |
| standard | UL Listed,Federal Specifications Classification W-C375B |