



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GHB3015 Type GHB BRKR 3P 15A 277/480VAC Max 125/250VDC Max *Eaton Corp*

Catalog Number	GHB3015
Manufacturer	Eaton Corp
Description	Molded Case Circuit Breaker, 15 A, Non-Interchangeable Thermal Magnetic Tripping Mechanism, 277/480 V Ac;125/250 V DC, G-Frame Frame, 50/60 HZ, 4 In Overall Height, 6.5 In Overall Length, 3.7 In Overall Width
Weight per unit	1.8 (lbs/each)
Product Category	3 Pole

### Features

Current Rating	15 A
dimensions	2.6300 IN X 3.0000 IN X 4.0000 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic

### Descriptions

Description	TYPE GHB BRKR 3P 15A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHB3015 GHB CB 3P 15A 277/480VA

### Manufacturer Information

GTIN	00786679911259
UPC	786679911259

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker

### Packaging

Carton	1
Weight Per each	1.75

### Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
standard	UL Listed,Federal Specifications Classification W-C375B