



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GL814 #8 1-Hole Compression Lug 1/4" Bolt

*Nsi Industries*

Catalog Number	GL814
Manufacturer	Nsi Industries
Description	Compression Connector, #8 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Red Insulation Color, +90 °C Operating Temperature, 1.201 In Overall Length, 600 V Ac, 0.02 LB/Ea
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	# 8 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	1/4
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Red
Finish	Tin Plated

### Dimensions and Weight

Size	L=1.20 - W=.420 - OD=.270 - ID=.170
------	-------------------------------------

### Descriptions

Description	#8 1-HOLE COMPRESSION LUG 1/4" BOLT
extra long description	NSI GL814 CU CMP Lug Short 8 AWG 1/
Features	1 HoleShort Barrel Copper Compression Lug w/ PeepHole8 AWG-1/4" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.

### Manufacturer Information

GTIN	00662381036018
UPC	662381036018

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - One Hole



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.02

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/4 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)