



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GL814 #8 1-Hole Compression Lug 1/4" Bolt

Nsi Industries

Catalog Number	GL814
Manufacturer	Nsi Industries
Description	Compression Connector, #8 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Red Insulation Color, +90 °C Operating Temperature, 1.201 In Overall Length, 600 V Ac, 0.02 LB/Ea
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	# 8 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	1/4
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Red
Finish	Tin Plated

Dimensions and Weight

Size	L=1.20 - W=.420 - OD=.270 - ID=.170
------	-------------------------------------

Descriptions

Description	#8 1-HOLE COMPRESSION LUG 1/4" BOLT
extra long description	NSI GL814 CU CMP Lug Short 8 AWG 1/
Features	1 HoleShort Barrel Copper Compression Lug w/ PeepHole8 AWG-1/4" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.

Manufacturer Information

GTIN	00662381036018
UPC	662381036018

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - One Hole



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/4 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)