



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GLA4 4-14 Lay-In Conn

*Nsi Industries*

Catalog Number	GLA4
Manufacturer	Nsi Industries
Description	Lay-In Connector, #14 Awg Conductor Size, #4 Awg Conductor Size, Non-Insulated, Aluminum/Copper Conductor Material, +90 °C Operating Temperature, 1.07 In Overall Length, 600 V Ac, 0.02 LB/Ea
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	1
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	4-14 AWG
Wire Type	Al/Cu

### Material, Color, and Finish

Color	Aluminum
Finish	Tin-Plated

### Dimensions and Weight

Size	L=1.07 - H=.750 - W=.380
------	--------------------------

### Descriptions

Description	4-14 LAY-IN CONN
extra long description	NSI GLA-4 Lay In Connector Aluminum
Features	Lay In Connector 4 - 14 AWG Lay-in connectors offer the ultimate in flexibility. Excellent for grounding and continuous loop applications. Made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600V (2000V max. per UL486B). UL 486A/B Listed. Temperature rating 90 degrees C.

### Manufacturer Information

GTIN	00662381001900
UPC	662381001900

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Aluminum Lay-In Lug



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	100
Weight Per each	0.02

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486A/B
Temperature Rating	90 C