



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GMA10A 10A 125V Fa 5X20MM Glass Fuse

Bussmann Fuses

Catalog Number	GMA10A
Manufacturer	Bussmann Fuses
Description	Buss Gma-10A UI Fast Acting 5MM Gla
Weight per unit	0.0040 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	10 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 2 Min Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	125 VAC

Dimensions and Weight

Size	5 mm Diameter X 20 mm Length
------	------------------------------

Descriptions

Description	10A 125V FA 5X20MM GLASS FUSE
Long Description	BUSS GMA-10A UL Fast Acting 5mm Gla
Product Type	UI Fast Acting 5MM Glass Fuse 10a
Special Features	Low Breaking Capacity, Interrupt Rating 200 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712716727
Manufacturers Part Number	GMA-10A
UPC	051712716727

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	1
Package	5
Weight Per each	0.004



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA, CE