



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GMA125MA 125MA 250V Fa 5X20MM Glass Fuse *Bussmann Fuses*

Catalog Number	GMA125MA
Manufacturer	Bussmann Fuses
Description	Buss Gma-125MA UI Fast Acting 5MM G
Weight per unit	0.0100 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	125 mA
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 2 Min Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	250 VAC

Dimensions and Weight

Size	5 mm Diameter X 20 mm Length
------	------------------------------

Descriptions

Description	125MA 250V FA 5X20MM GLASS FUSE
Long Description	BUSS GMA-125MA UL Fast Acting 5mm G
Product Type	UI Fast Acting 5MM Glass Fuse 125ma
Special Features	Low Breaking Capacity, Interrupt Rating 35 Amp at 250 Vac, 10 kA at 125 Vac, Material Glass Tube, Silver Plated Brass End Cap

Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712716604
Manufacturers Part Number	GMA-125MA
UPC	051712716604

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	5
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA, CE