



Powering Business Worldwide

pe.eaton.com

Medium Time-Delay Fuse

BK/GMC-6.3-R

UPC:051712642293

Dimensions:

- **Height:** .788 IN
- **Length:** .197 IN
- **Width:** .197 IN

Weight:.002 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 6.3A
- **Voltage Rating:** 125 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 200 AIC at 125 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** out axial leads
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end
- **Quantity:** Bulk 100

Supporting documents: No Data

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant

