



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GMEV32BRWC Ev Wall Charger Kit 32A BR 2P 40a

Eaton Corp

Catalog Number	GMEV32BRWC
Manufacturer	Eaton Corp
Description	Eaton Green Motion Ev Wall Charger Hardwired, 32A, BR 2P, 40a
Weight per unit	15.0 (lbs/each)
Product Category	Distribution Equipment

Features

amperage rating	40 A
dimensions	10.7400 IN X 4.4200 IN X 15.1200 IN
Voltage Rating	208-240 Vac

Descriptions

Description	EV WALL CHARGER KIT 32A BR 2P 40A
extra long description	ETN GMEV32BR-WC EV Wall Charger Kit
Features	The future of transportation is electric. While that changes how vehicles are powered, it does not require you to adjust your driving habits or pay a premium on your electric bill. Instead, fast and cost-effective charging is a must. Enter Green Motion EV smart breaker chargers-fast AC charging, powered by smart breakers. Eaton chargers deliver real-time energy insights and enable integration with onsite renewable and energy storage systems to advance smart and sustainable energy systems to power today and
Long Description	Eaton Green Motion EV wall charger hardwired, 32A, BR 2P, 40A
Product Type	Ev Wall Charger Kit 32A, BR 2P 40a

Manufacturer Information

Brand	Eaton
GTIN	00786689667658
Manufacturers Part Number	GMEV32BR-WC
UPC	786689667658

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	EV wall charger

Packaging

Carton	1
Weight Per each	15



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -
OtherCommercial / Institutional Buildings / Structures - Power
Distribution and ControlsResidential Bldgs & Facilities -
Residential Bldgs/Facilities - Aftermarket

standard

UL 489