


GT500R

Gotcha Sensor with two weatherproof, corrosionproof floodlights, molded gaskets and corrosionproof universal cover plate. Lamps not supplied.

Color: Black

Weight: 2.0 lbs



Technical Specifications

UL Listing:

Suitable for wet locations.

Voltage:

120 volts AC 60 Hz.

Power Consumption:

1 watt.

Time Adjustment:

10 seconds to 5 minutes.

Surge Protection:

Withstands up to 6000 volts.

Photoelectric Control:

Deactivates lights during daylight.

Detector Sensitivity:

Adjustable from 100% to 50%.

Wall Switch Manual Override:

Two flip logic prevents activation by momentary power outages. Override resets to auto after 6 hours or at dawn. No extra wiring needed.

Sensor Housing:

Made of tough, corrosion resistant polycarbonate.

Floodlights:

Made of tough, corrosion-resistant polycarbonate. For extra or replacement floodlights, order cat# TUFFY in your choice of color. Accepts PAR-38 lamps, medium base, 150 watts max. Lamps not included.

Detection:

110° view.

Patents:


RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

GT500R

Gotcha Sensor with two weatherproof, corrosionproof floodlights, molded gaskets and corrosionproof universal cover plate. Lamps not supplied.

Color: Black

Weight: 2.0 lbs



Technical Specifications

UL Listing:

Suitable for wet locations.

Voltage:

120 volts AC 60 Hz.

Power Consumption:

1 watt.

Time Adjustment:

10 seconds to 5 minutes.

Surge Protection:

Withstands up to 6000 volts.

Photoelectric Control:

Deactivates lights during daylight.

Detector Sensitivity:

Adjustable from 100% to 50%.

Wall Switch Manual Override:

Two flip logic prevents activation by momentary power outages. Override resets to auto after 6 hours or at dawn. No extra wiring needed.

Sensor Housing:

Made of tough, corrosion resistant polycarbonate.

Floodlights:

Made of tough, corrosion-resistant polycarbonate. For extra or replacement floodlights, order cat# TUFFY in your choice of color. Accepts PAR-38 lamps, medium base, 150 watts max. Lamps not included.

Detection:

110° view.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.