



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



H1499TAT *Delisted* 4" At Non-Ic SHLW CLNG 12V Low Volt *Cooper Lighting Solutions*

Catalog Number	H1499TAT
Manufacturer	Cooper Lighting Solutions
Description	4" Housing Non-Ic, Air-Tite Shallow Ceiling 12V Low Voltage, MR16
Weight per unit	2.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.50A
Ballast Type	N/A
Lamp Type	N/A
Number of Lamps	1
Voltage Rating	120-277V
Wattage	57W

Descriptions

Description	4" AT NON-IC SHLW CLNG 12V LOW VOLT
extra long description	CLS H1499TAT 4IN NON-IC LOW VOLTAGE
Long Description	4" Housing Non-IC, Air-Tite Shallow Ceiling 12V Low Voltage, MR16
Product Type	4IN Non-Ic Low Voltage Housing
Special Features	Got Nail!™ bar hangers

Manufacturer Information

Brand	HALO
GTIN	00080083584383
Manufacturers Part Number	H1499TAT
UPC	080083584383

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	4" H1499 Low Voltage Housing

Packaging

Carton	1
Package	6
Weight Per each	2

Uses, Certifications, and Standards

Application	lighting
standard	UL/cUL Listed - Damp Location;UL/cUL Listed - Wet Location;Airtite