



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



H38JA100DX 100W ED23.5 Mercury Vapor White Mogul Base Lamp *Sylvania-Ledvance*

Catalog Number	H38JA100DX
Manufacturer	Sylvania-Ledvance
Description	Syl H38JA-100/DX/69408 H38JA100DX 2
Weight per unit	0.4600 (lbs/each)
Product Category	Lighting

Features

Base	E39
Shape	ET23.5
Voltage Rating	120-277
Wattage	47

Material, Color, and Finish

color rendering index (cri)	45
color temperature	4000.0000000000000000
Finish	COATED

Descriptions

Description	100W ED23.5 MERCURY VAPOR WHITE MOGUL BASE LAMP
Long Description	SYL H38JA-100/DX/69408 H38JA100DX 2
Product Type	H38JA100DX 20/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135694080
Manufacturers Part Number	H38JA-100/DX/69408
UPC	046135694080

Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
Type	High Intensity Discharge (HID)

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	12
Weight Per each	0.46



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

H38
