



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



H38LVICAT 3" Low Voltage Ic At Can

Cooper Lighting Solutions

Catalog Number	H38LVICAT
Manufacturer	Cooper Lighting Solutions
Description	3" Housing Ic Air-Tite 12V Low Voltage, MR16
Weight per unit	6.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	4.167 at (12V)
Ballast Type	N/A
Lamp Type	MR16
Number of Lamps	1
Voltage Rating	120V
Wattage	50W

Descriptions

Description	3" LOW VOLTAGE IC AT CAN
extra long description	CLS H38LVICAT 3" HOUS IC AIR-TITE 1
Long Description	3" HOUSING IC AIR-TITE 12V LOW VOLTAGE, MR16
Product Type	3" Hous Ic Air-Tite 12V LW VLTG, MR16
Special Features	Got-Nail™ bar hangers

Manufacturer Information

Brand	HALO
GTIN	00623961361289
Manufacturers Part Number	H38LVICAT
UPC	623961361289

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	3" H3 Low Voltage Housing

Packaging

Carton	1
Weight Per each	6

Uses, Certifications, and Standards

Application	lighting
standard	UL/cUL Listed - Damp Location;Airtite