



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL1221R SP Tog, Ind GRD, 20A 120/277V, RD *Hubbell Wiring Devices*

Catalog Number	HBL1221R
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose Ac, Single Pole, 20A 120/277V Ac, Back and Side Wired, Red Toggle
Weight per unit	0.0770 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Positive Snap
amperage rating	20
connection	Back and Side Wired
Contact Configuration	Two Position
Contact Rating	Per UL 20
Current Rating	20
insulation	False
operating cycles	50,000
pallet quantity	4500
Poles	Single Pole
Switch Type	Toggle
Voltage Rating	120-277
Wattage	5540

Dimensions and Weight

Size	4.06 in x 1.31 in x 1.87 in
------	-----------------------------

Descriptions

Description	SP TOG, IND GRD, 20A 120/277V, RD
extra long description	HWDK HBL1221R SP TOG, IND GRD, 20A
Long Description	Switches and Lighting Controls, Extra Heavy Duty Industrial Grade, Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired, Red Toggle
Product Type	SP Tog, Ind GRD, 20A 120/277V, RD
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585431567
Manufacturers Part Number	HBL1221R
series	Extra Heavy Duty
UPC	783585431567



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	TOGGLE

Packaging

Carton	1
Package	10
Weight Per each	0.077

Uses, Certifications, and Standards

Application	Back and Side Wired
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed