ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# HBL2310ST Locking Recp 20A 125V L5-20R BK Spring T

*Hubbell Incorporated Delaware*

| | |
|---|---|
| Catalog Number | HBL2310ST |
| Manufacturer | Hubbell Incorporated Delaware |
| Description | 20A, 125V Edgeconnect™ Twist-Lock® Receptacle With Spring Termination |
| Weight per unit | 0.1510 (lbs/each) |
| Product Category | Wiring Devices |

## Features

| | |
|---|---|
| connection | Spring Termination |
| Dielectric Strength | Withstands 2,000V minimum |
| insulation | False |
| Material | Nylon |
| Number of Wires | 3 |
| pallet quantity | 2250 |
| Phase | 1 |
| Poles | 2 |
| Voltage Rating | 125 V |
| Wattage | 2,500 |
| Wire Size | 14 - 10 solid, 14 - 8 stranded (including compact stranded) |

## Dimensions and Weight

| | |
|---|---|
| Size | 3.28 in x 1.70 in x 1.47 in |

## Descriptions

| | |
|---|---|
| Description | LOCKING RECP 20A 125V L5-20R BK SPRING T |
| extra long description | HWDK HBL2310ST LKG RCPT, 20A 125V, |
| Long Description | 20A, 125V EdgeConnect™ Twist-Lock® Receptacle with Spring Termination |
| Product Type | LKG RCPT, 20A 125V, L5-20R, BK, Spring T |
| Special Features | Twist-Lock Receptacle with Spring Termination |

## Manufacturer Information

| | |
|---|---|
| Brand | WIRING DEVICE-KELLEMS |
| GTIN | 00783585569543 |
| Manufacturers Part Number | HBL2310ST |
| UPC | 783585569543 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Industrial receptacles |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 30 |
| Weight Per each | 0.151 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Heavy Duty Industrial |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting | Screw Mount |
| nema rating | L5-20R |
| standard | CSA Certified to Specification C22.2 No. 42;UL Listed To UL 498;WR Rating |