ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2613 Locking Conn 30A 125V L5-30R B/W

Hubbell Incorporated Delaware

Catalog Number	HBL2613
Manufacturer	Hubbell Incorporated Delaware
Description	Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Black and White.
Weight per unit	0.3500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
connection	Pressure Screw Terminal
Current Rating	30
insulation	Insulated Body
Material	Nylon
Number of Conductors	3
pallet quantity	2400
Poles	2-Pole
Voltage Rating	125

Material, Color, and Finish

Color	Black;White

Dimensions and Weight

Size	2.26 in x 2.26 in x 3.86 in

Descriptions

Description	LOCKING CONN 30A 125V L5-30R B/W
extra long description	HWDK HBL2613 LKG CONN, 30A 125V, L5
Long Description	Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Black and White.
Product Type	LKG Conn, 30A 125V, L5-30R, B/W
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585038766
Manufacturers Part Number	HBL2613
UPC	783585038766

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Connector Body

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L5-30R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498