



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2615SW LKG WT S/SHRD FLG-Inlt, 30A 125V, L5-30P *Hubbell Wiring Devices*

Catalog Number	HBL2615SW
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Gray.
Weight per unit	0.5500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
connection	Screw Terminals
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
insulation	True
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 VAC
Wattage	3,750
Wire Size	#16 to #8

Dimensions and Weight

Size	3.75 in x 3.75 in x 2.27 in
------	-----------------------------

Descriptions

Description	LKG WT S/SHRD FLG-INLT, 30A 125V, L5-30P
extra long description	HWDK HBL2615SW LKG WT S/SHRD FLG-IN
Long Description	Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Gray.
Product Type	LKG WT S/SHRD FLG-Inlt, 30A 125V, L5-30P
Special Features	Shrouded Watertight Construction

Manufacturer Information

Brand	Hubbell Wiring Devices
GTIN	00783585231648
Manufacturers Part Number	2615SW
UPC	783585231648

Taxonomies, Classifications, and Categories

Category Description	Poles & Accessories
Type	Flanged Inlet



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.55

Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Watertight
Mounting	Screw Mount
nema rating	L5-30P
standard	UL Listed, CSA Certified To Type 4, 4X And Type 12