



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL4560 LKG SGL RCPT, 15A 250V, L6-15R, BK *Hubbell Wiring Devices*

Catalog Number	HBL4560
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, Nema L6-15R, Screw Terminal, Black.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15
connection	Screw Terminal
Current Rating	15
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	3,750
Wire Size	#18 to #10

### Dimensions and Weight

Size	3.28 in x 1.53 in x 1.27 in
------	-----------------------------

### Descriptions

Description	LKG SGL RCPT, 15A 250V, L6-15R, BK
extra long description	HWDK HBL4560 LKG SGL RCPT, 15A 250V
Long Description	Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, NEMA L6-15R, Screw Terminal, Black.
Product Type	LKG SGL RCPT, 15A 250V, L6-15R, BK
Special Features	Standard

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585236605
Manufacturers Part Number	HBL4560
UPC	783585236605

### Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	RECEPTACLE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.15

## Uses, Certifications, and Standards

Application ..... Heavy Duty Industrial

environmental conditions ..... Indoor Dry unless protected by additional means

Mounting ..... Screw Mount

nema rating ..... L6-15R

standard ..... Certified to CSA C22.2 No.42;Fed. Spec. W-C-596;Listed to UL 498