



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL5666C Plug, 15A 250V, 6-15P, B/W *Hubbell Wiring Devices*

Catalog Number	HBL5666C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 250V, 6-15P, Black and White, Single Pack.
Weight per unit	0.0490 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	15
Material	COMPOSITE
Number of Wires	3-Wire
pallet quantity	6600
Phase	1
Poles	2-Pole
Voltage Rating	250
Wattage	3
Wire Size	#18 to #10

Dimensions and Weight

Size	1.97 in x 1.53 in x 1.53 in
------	-----------------------------

Descriptions

Description	PLUG, 15A 250V, 6-15P, B/W
extra long description	HWDK HBL5666C PLUG, 15A 250V, 6-15P
Long Description	Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 250V, 6-15P, Black and White, Single Pack.
Product Type	Plug, 15A 250V, 6-15P, B/W
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585175607
Manufacturers Part Number	HBL5666C
series	Insulgrip®
UPC	783585175607



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	PLUG

Packaging

Carton	1
Package	10
Weight Per each	0.049

Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Ribbed Nylon Housing Is Impact and Chemical Resistant
Mounting	Cord
nema rating	6-15P
standard	CSA Certified to C22.2 No. 42 File 280;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706