



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL8410 SGL RCPT, 3P4W, 20A 125/250V, 14-20R, BK** *Hubbell Wiring Devices*

Catalog Number	HBL8410
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 3-Pole 4-Wire Grounding, 20A 125/250V, 14-20R, Black, Single Pack.
Weight per unit	0.2500 (lbs/each)
Product Category	Wall Plates & Covers

### **Features**

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	4-Wire
Phase	1
Poles	3-Pole
Voltage Rating	125/250 V
Wattage	5000
Wire Size	#14 to #10

### **Dimensions and Weight**

Size	2.44 in x 1.5 in x 1.24 in
------	----------------------------

### **Descriptions**

Description	SGL RCPT, 3P4W, 20A 125/250V,14-20R,BK
extra long description	HWDK HBL8410 SGL RCPT, 3P4W, 20A 12
Long Description	Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 3-Pole 4-Wire Grounding, 20A 125/250V, 14-20R, Black, Single Pack.
Product Type	SGL RCPT, 3P4W, 20A 125/250V, 14-20R, BK
Special Features	Self Grounding

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015705
Manufacturers Part Number	HBL8410
series	Extra Heavy Duty
UPC	783585015705



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	RECEPTACLE

## Packaging

Carton	1
Package	10
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Extra Heavy Duty Hospital Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	14-20R
standard	CSA Certified to C22.2 No. 42 File 280C;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706