



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL8430A SGL RCPT, 3P4W, 30A 3PH 250V, 15-30R, BK** *Hubbell Wiring Devices*

Catalog Number	HBL8430A
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 3-Pole 4-Wire Grounding, 30A 3 Phase 250V Ac, 15-30R, Black, Single Pack.
Weight per unit	0.2110 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### **Features**

amperage rating	30
connection	Back and Side Wired Screw Terminals
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	4-Wire
pallet quantity	1860
Phase	3
Poles	3-Pole
Voltage Rating	250 VAC
Wattage	7500
Wire Size	#12 to #6

### **Dimensions and Weight**

Size	Standard Sized Product
------	------------------------

### **Descriptions**

Description	SGL RCPT, 3P4W, 30A 3PH 250V,15-30R,BK
extra long description	HWDK HBL8430A SGL RCPT, 3P4W, 30A 3
Long Description	Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 3-Pole 4-Wire Grounding, 30A 3 Phase 250V AC, 15-30R, Black, Single Pack.
Product Type	SGL RCPT, 3P4W, 30A 3PH 250V, 15-30R, BK
Special Features	Standard

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015149
Manufacturers Part Number	HBL8430A
UPC	783585015149



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	SINGLE RECEPTACLE

## Packaging

Carton	1
Package	5
Weight Per each	0.211

## Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	15-30R
standard	Certified to CSA;NEMA® WD-6 Compliant;UL Listed File E2186