



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBLDS3AC Disconnect, 30A Unfused, 4X, W/Ac *Hubbell Wiring Devices*

Catalog Number	HBLDS3AC
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V Ac, Screw Terminals, Gray, Nema 4XENCLOSURE, With Aux Contact
Weight per unit	2.6 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

Features

action	Snap
amperage rating	30
connection	Terminal Screws
Contact Configuration	Two Position
Contact Rating	30A
Current Rating	30
Material	COMPOSITE
operating cycles	6,000
pallet quantity	410
Poles	3
Switch Type	Lever
Voltage Rating	600
Wattage	18000;18000.0000

Dimensions and Weight

Size	8.5 in x 6 in x 4.12 in
------	-------------------------

Descriptions

Description	DISCONNECT, 30A UNFUSED, 4X, W/AC
extra long description	HWDK HBLDS3AC DISCONNECT, 30A UNFUS
Features	NEC section 430.102(B) requires each motor controller to have a disconnect within line of sight from the motor and driven equipment. Hubbell's Circuit-Lock® Unfused Disconnect Switches are UL listed as a manual motor controller and also "suitable as a motor disconnect" and meet these code requirements.
Long Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA 4XEnclosure, With Aux Contact
Product Type	Disconnect, 30A Unfused, 4X, W/AC
Special Features	Standard Product with HBLAC1 Aux Contact



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585430607
Manufacturers Part Number	HBLDS3AC
series	Non-Fused
UPC	783585430607

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Disconnect Switches

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	2.6

Uses, Certifications, and Standards

Application	Labelless
Enclosure	Type 4X, IP69k
environmental conditions	NEMA 4X
Mounting	Mounting Feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
standard	UL Listed