



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBLEDLD524SEWUNV Hbledld524sewunvl850ed2u *Cooper Lighting Solutions*

Catalog Number	HBLEDLD524SEWUNV
Manufacturer	Cooper Lighting Solutions
Description	Led High Bay Light, White Enamel, CRS;Aluminum, 120/277 V Ac, 0.542 A @ 277 V, 149 W, >60000 H Average Life, 22339 LM Brightness (Lumens), 5000 K, 70;80, Dimmable, Wide Beam Spread, Surface/Chain Mount, 48-1/2 In Length, 20-3/16 In Width, 2-3/8 In Height, 5 Yr Warranty, 24 LB
Weight per unit	24.0 (lbs/each)
Product Category	Led Highbay Lighting

Features

amperage rating	0.542 at 277V
Ballast Type	N/A
Lamp Type	LED

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	HBLEDLD524SEWUNVL850ED2U
extra long description	CLS HBLED-LD5-24SE-W-UNV-L850-ED2-U

Manufacturer Information

Brand	METALUX
GTIN	00080083788668
Manufacturers Part Number	HBLED-LD5-24SE-W-UNV-L850-ED2-
UPC	080083788668

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	INDUSTRIAL

Packaging

Carton	1
Weight Per each	24

Uses, Certifications, and Standards

Mounting	Surface Mount
standard	cUL Listed - Damp Location;RoHS Compliant;DLC Qualified