



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HF0924414 24V, 70CFM SDMT FLTR Fan

Hoffman Enclosures, Inc.

Catalog Number	HF0924414
Manufacturer	Hoffman Enclosures, Inc.
Description	HF09 Side-Mount Filter Fan, 24V 70CFM, LT Gray
Weight per unit	3.2 (lbs/each)
Product Category	20180212140122

Features

Ambient Temperature	-4 to 149 deg F
amperage rating	0.35 A
flow rate	70 CFM
Material	Plastic
nominal voltage	24
Voltage Rating	24 VDC

Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Housing Material	Non-metallic

Dimensions and Weight

Size	8.19 x 8.21 x 4.15 in
------	-----------------------

Descriptions

Description	24V,70CFM SDMT FLTR FAN
extra long description	NVENT HOF HF0924414 IP54 9 in FF 24
Features	HF Side-Mount Filter Fans quickly install into enclosure with a click-fit design; no tools or screws required. Grilles open with the flick of a finger for easy filter replacement.
Long Description	HF09 Side-Mount Filter Fan, 24V 70CFM, Lt Gray
Product Type	IP54 9 In FF 24V 7035

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510341978
Manufacturers Part Number	HF0924414
UPC	783510341978

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Fans and Filter Fans



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton.....	1.....
Weight Per each.....	3.18.....

Uses, Certifications, and Standards

Application.....	Controls and Drives; Power Distribution.....
------------------	----------------------------------------------