



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HF1016414 10", 115V S-MT FLTR Fan

*Hoffman Enclosures, Inc.*

Catalog Number	HF1016414
Manufacturer	Hoffman Enclosures, Inc.
Description	HF10 Side-Mount Filter Fan, 115V 159CFM, LT Gray
Weight per unit	3.1 (lbs/each)
Product Category	20160927104906

### Features

Ambient Temperature	14 to 131 deg F
amperage rating	0.38/0.36 A
flow rate	159 CFM
Material	Plastic
nominal voltage	115
Voltage Rating	115 VAC

### Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Housing Material	Non-metallic

### Dimensions and Weight

Size	10.13 x 10.14 x 4.68 in
------	-------------------------

### Descriptions

Description	10", 115V S-MT FLTR FAN
extra long description	NVENT HOF HF1016414 IP54 10 in FF 1
Features	HF Side-Mount Filter Fans quickly install into enclosure with a click-fit design; no tools or screws required. Grilles open with the flick of a finger for easy filter replacement.
Long Description	HF10 Side-Mount Filter Fan, 115V 159CFM, Lt Gray
Product Type	IP54 10 In FF 115V 7035

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510342036
Manufacturers Part Number	HF1016414
UPC	783510342036

### Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Fans and Filter Fans



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	3.09

## Uses, Certifications, and Standards

Application	Power Distribution; Controls and Drives
-------------	---