

NEER Zinc Pulling Ells and PVC Entrance Caps

Threaded for Rigid Conduit and IMC

HL: 90° Female/Female Pulling Ells

Applications

- Threaded 90° corner pulling elbows are used to facilitate pulling conductors through a sharp bend in a run of threaded rigid conduit or IMC.

Features

- Raintight (wet locations).
- The removable cover gives ample access so that wire pulling can be achieved without any obstructions.

Standard Material


- Zinc diecast

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1



HL-500



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		A	B
1/2	HL-500	2.10/53.3	2.10/53.3
3/4	HL-750	2.29/58.2	2.29/58.2

PVC: Entrance Caps

Applications

- Plastic entrance caps for rigid conduit, IMC, EMT or PVC conduit service mast.

Features

- Cover releases with screwdriver twist, no screws to back out.
- U-slots eliminate cumbersome two piece insulator.
- Complete with EMT adapter.

Standard Material


- PVC

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E302405
- NEMA: FB-1



PVC-100



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		A	B
1/2	PVC-100	2.90/73.7	2.63/66.8
3/4	PVC-101	3.17/80.5	3.15/80.0
1	PVC-102	3.35/85.1	3.11/79.0
1-1/4	PVC-103	3.90/99.1	3.70/94.0
1-1/2	PVC-104	3.80/96.5	3.77/95.8
2	PVC-105	6.25/158.8	6.50/165.1

NEER Zinc Pulling Ells and PVC Entrance Caps

Threaded for Rigid Conduit and IMC

HL: 90° Female/Female Pulling Ells

Applications

- Threaded 90° corner pulling elbows are used to facilitate pulling conductors through a sharp bend in a run of threaded rigid conduit or IMC.

Features

- Raintight (wet locations).
- The removable cover gives ample access so that wire pulling can be achieved without any obstructions.

Standard Material


- Zinc diecast

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1



HL-500



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		A	B
1/2	HL-500	2.10/53.3	2.10/53.3
3/4	HL-750	2.29/58.2	2.29/58.2

PVC: Entrance Caps

Applications

- Plastic entrance caps for rigid conduit, IMC, EMT or PVC conduit service mast.

Features

- Cover releases with screwdriver twist, no screws to back out.
- U-slots eliminate cumbersome two piece insulator.
- Complete with EMT adapter.

Standard Material


- PVC

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E302405
- NEMA: FB-1



PVC-100



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		A	B
1/2	PVC-100	2.90/73.7	2.63/66.8
3/4	PVC-101	3.17/80.5	3.15/80.0
1	PVC-102	3.35/85.1	3.11/79.0
1-1/4	PVC-103	3.90/99.1	3.70/94.0
1-1/2	PVC-104	3.80/96.5	3.77/95.8
2	PVC-105	6.25/158.8	6.50/165.1