



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLBC6LS9FSD2W1EM 6" Led Slim DWNLT CCT Canless or Retrofit 120V

Cooper Lighting Solutions

Catalog Number	HLBC6LS9FSD2W1EM
Manufacturer	Cooper Lighting Solutions
Description	6" Downlight, 900/1100 Selectable Lumens 90 Cri Selectable CCT D2W Option 120V 60HZ Le & Te Phase Cut 5 Percent Dimming Matte White Flange Canless or Retrofit Installation Compliant All States But Ca
Weight per unit	2.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.13A at 120V
Lamp Type	LED
Socket Type	N/A
Voltage Rating	120V
Wattage	16 W

Material, Color, and Finish

Finish	Matte White
Style	(blank)

Descriptions

Description	6" LED SLIM DWNLT CCT CANLESS OR RETROFIT 120V
extra long description	CLS HLBC6LS9FSD2W1EMWR 6" HLB COMFO
Long Description	6" downlight, 900/1100 selectable lumens 90 CRI selectable CCT D2W option 120V 60Hz LE & TE phase cut 5 percent dimming matte white flange canless or retrofit installation compliant all states but CA
Product Type	6" HLB Comfort, 900-1100LM, 5CCT, D2W, R
Special Features	Available in 4" and 6"

Manufacturer Information

Brand	Cooper Lighting Solutions
GTIN	00080083263219
Manufacturers Part Number	HLBC6LS9FSD2W1EMWR
UPC	080083263219

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	HLBC Slim Regressed Canless Downlight

Packaging

Carton	1
Weight Per each	2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	CEILING
standard	Energy Star Certified; IECC Compliant; Title 20 Compliant; Title 24 Compliant; UL Listed; RoHS Compliant