

HLF1 & HLF2

High-Lumen Flood LED Luminaires

The Solution You Need

The HLF high-lumen floodlights from Lithonia Lighting are the ideal LED solution for replacing 400W and 1000W metal halide floodlights by delivering what you need – a no-compromise solution that saves energy and lowers maintenance costs.



A No-Compromise Solution

With up to 64,000 lumens, the HLF high-lumen floodlight produces enough light to replace up to 1000W metal halide floodlights with ease. Combine this power with easy mounting options, such as our universal slipfitter or yoke mounts, and you can retrofit virtually any existing 1000W HID floodlight installation.

Energy Savings

The HLF provides typical energy savings of 54% when replacing 1000W metal halide without sacrificing light levels. Combine this with Acuity Controls ROAM® for site-wide dimming and monitoring—and the energy savings are even greater.

Lower Maintenance Costs

With a life expectancy of over 20 years, the HLF is designed to save money. Eliminating up to ten expensive metal halide lamp changes over the life of the product, maintenance costs are virtually eliminated. This is especially important at hard-to-reach mounting heights where lamp-replacement costs are inconvenient and expensive.

Quick Facts:

- Replaces 400W and 1000W metal halide floodlights
- Lumen packages ranging from 19,000 to 64,000
- Eight optics designed to meet unique application requirements, including a 7° optic
- Universal yoke and integral slip fitter mounting options for easy 1-for-1 retrofit
- Instant-on, avoiding long restrike times of traditional HID sources




HLF1 & HLF2

Ordering Information

EXAMPLE: HLF2 LED P1 40K WFL MVOLT IS DDBXD

HLF1 & HLF2													
Series	Package	Color temperature		Distribution		Voltage	Mounting		Options	Finish			
HLF1 LED	P1	30K	3000 K	VNSP	Very Narrow Spot	MVOLT	Shipped included		Shipped installed		DDBXD	Dark bronze	
HLF2 LED	P2	40K	4000 K	NSP	Narrow Spot	120	IS	Integral slipfitter (fits 2-3/8" O.D. tenon)	PER5	NEMA twist-lock receptacle only (no controls)	DBLXD	Black	
	P3	50K	5000 K	SP	Spot	208	YKC62	Yoke with 16-3 SO cord	SF	Single fuse (120, 277, 347V)	DNAXD	Natural aluminum	
				NFL	Narrow Flood	240			DF	Double fuse (208, 240, 480V)	DWHXD	White	
	MNFL	Medium Narrow Flood	277						CFB	Black faceplate			
	MFL	Medium Flood	347						Shipped separately				
	WFL	Wide Flood	480						UBV	Upper/bottom visor accessory			
									FV	Full Baffle accessory			
									VG	Vandal guard accessory (polycarbonate)			
									WG	Wire guard accessory			
						HLF1 (4000K, MFL)			HLF2 (4000K, MFL)			*Consult product spec sheet for more details	
Performance Package		Lumens	Input Watts	LPW	Lumens	Input Watts	LPW						
P1		19,370	166W	117	39,250	328W	120						
P2		27,354	246W	111	53,847	487W	111						
P3		32,638	295W	111	64,248	598W	107						

Optic Options



LED Floodlighting Solutions

D-Series Floods

50W - 400W Metal Halide Replacement

HLF High-Lumen Floods

400W - 1000W Metal Halide Replacement

MODEL #	DSXF1	DSXF2	DSXF3	HLF1	HLF2
Lumens	3,977	7,670	18,992	32,638	64,248
Metal Halide Replacement	50W - 150W	150W - 250W	250W - 400W	400W+	1000W+
Input Watts	37W	74W	183W	295W	598W
LPW	107	104	104	111	107
DesignLights Consortium® qualified product	✓	✓	✓	✓	✓

Learn more about our LED floodlighting solutions at www.lithonia.com

HLF1 & HLF2

High-Lumen Flood LED Luminaires

The Solution You Need

The HLF high-lumen floodlights from Lithonia Lighting are the ideal LED solution for replacing 400W and 1000W metal halide floodlights by delivering what you need – a no-compromise solution that saves energy and lowers maintenance costs.



A No-Compromise Solution

With up to 64,000 lumens, the HLF high-lumen floodlight produces enough light to replace up to 1000W metal halide floodlights with ease. Combine this power with easy mounting options, such as our universal slipfitter or yoke mounts, and you can retrofit virtually any existing 1000W HID floodlight installation.

Energy Savings

The HLF provides typical energy savings of 54% when replacing 1000W metal halide without sacrificing light levels. Combine this with Acuity Controls ROAM® for site-wide dimming and monitoring—and the energy savings are even greater.

Lower Maintenance Costs

With a life expectancy of over 20 years, the HLF is designed to save money. Eliminating up to ten expensive metal halide lamp changes over the life of the product, maintenance costs are virtually eliminated. This is especially important at hard-to-reach mounting heights where lamp-replacement costs are inconvenient and expensive.

Quick Facts:

- Replaces 400W and 1000W metal halide floodlights
- Lumen packages ranging from 19,000 to 64,000
- Eight optics designed to meet unique application requirements, including a 7° optic
- Universal yoke and integral slip fitter mounting options for easy 1-for-1 retrofit
- Instant-on, avoiding long restrike times of traditional HID sources




HLF1 & HLF2

Ordering Information

EXAMPLE: HLF2 LED P1 40K WFL MVOLT IS DDBXD

HLF1 & HLF2											
Series	Package	Color temperature		Distribution		Voltage	Mounting	Options	Finish		
HLF1 LED	P1	30K	3000 K	VNSP	Very Narrow Spot	MVOLT	Shipped included	Shipped installed	DDBXD	Dark bronze	
HLF2 LED	P2	40K	4000 K	NSP	Narrow Spot	120	IS	Integral slipfitter (fits 2-3/8" O.D. tenon)	PER5	NEMA twist-lock receptacle only (no controls)	
	P3	50K	5000 K	SP	Spot	208	YKC62	Yoke with 16-3 SO cord	SF	Single fuse (120, 277, 347V)	
				NFL	Narrow Flood	240			DF	Double fuse (208, 240, 480V)	
				MNFL	Medium Narrow Flood	277			CFB	Black faceplate	
				MFL	Medium Flood	347			Shipped separately		
				WFL	Wide Flood	480			UBV	Upper/bottom visor accessory	
									FV	Full Baffle accessory	
									VG	Vandal guard accessory (polycarbonate)	
									WG	Wire guard accessory	
				HLF1 (4000K, MFL)			HLF2 (4000K, MFL)			*Consult product spec sheet for more details	
Performance Package		Lumens	Input Watts	LPW	Lumens	Input Watts	LPW				
P1		19,370	166W	117	39,250	328W	120				
P2		27,354	246W	111	53,847	487W	111				
P3		32,638	295W	111	64,248	598W	107				

Optic Options



LED Floodlighting Solutions

D-Series Floods

50W - 400W Metal Halide Replacement

HLF High-Lumen Floods

400W - 1000W Metal Halide Replacement

MODEL #	DSXF1	DSXF2	DSXF3	HLF1	HLF2
Lumens	3,977	7,670	18,992	32,638	64,248
Metal Halide Replacement	50W - 150W	150W - 250W	250W - 400W	400W+	1000W+
Input Watts	37W	74W	183W	295W	598W
LPW	107	104	104	111	107
DesignLights Consortium® qualified product	✓	✓	✓	✓	✓

Learn more about our LED floodlighting solutions at www.lithonia.com