



HLS6099501EWH6BP 6" 15W Led Disk Light 50K 90CRI 120V 900LM 6 Pack

Cooper Lighting Solutions

Catalog Number	HLS6099501EWH6BP
Manufacturer	Cooper Lighting Solutions
Description	6" Led Surface Light, 900 Lumens (Nominal), 90 Cri Minimum, 5000K CCT, 120V 60HZ, Le and Te Phase, Matte White Flange Cut 10 Percent Dimming, Qty 6 Bulk Pack (Not For Individual Sale)
Weight per unit	3.9 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.13
Lamp Type	LED
Voltage Rating	120V
Wattage	15.6

Material, Color, and Finish

Finish	Matte
Style	(blank)

Descriptions

Description	6" 15W LED DISK LIGHT 50K 90CRI 120V 900LM 6 PACK
extra long description	CLS HLS6099501EWH-6BP HLS, 6IN, 900
Long Description	6" LED surface light, 900 lumens (nominal), 90 CRI minimum, 5000K CCT, 120V 60Hz, LE and TE phase, matte white flange cut 10 percent dimming, Qty 6 bulk pack (not for individual sale)
Product Type	HLS, 6IN, 900LM, 5000K, Wet, 6PK
Special Features	Round 4-, 6-, 9-, and 9-inch motion low-profile surface mount fixtures for residential downlighting

Manufacturer Information

Brand	HALO
GTIN	00080083256822
Manufacturers Part Number	HLS6099501EWH-6BP
UPC	080083256822

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLS Round LED Surface Mount

Packaging

Carton	1
Package	6
Weight Per each	3.94



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

lighting

Mounting

SURFACE

standard

Energy Star;IECC Compliant;RoHS Compliant;Title 24
Compliant;UL Listed