



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLSMS9129301EWH 9" 18W Led Disc Light 30K W/Motion Sensor 1200LM

Cooper Lighting Solutions

Catalog Number	HLSMS9129301EWH
Manufacturer	Cooper Lighting Solutions
Description	9" Motion Sensor, Led Surface Light, 1200 Lumens (Nominal), 90 Cri Minimum, 3000K CCT, 120V 60HZ, Le and Te Phase, Matte White Flange Cut 10 Percent Dimming, Compliant In All States Except California
Weight per unit	1.3 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.147A
Lamp Type	LED
Socket Type	N/A
Voltage Rating	120V
Wattage	17.7 W

Material, Color, and Finish

Finish	Matte White
Style	(blank)

Descriptions

Description	9" 18W LED DISC LIGHT 30K W/MOTION SENSOR 1200LM
extra long description	CLS HLSMS9129301EWH HLS, 9IN, 1200L
Long Description	9" motion sensor, LED surface light, 1200 lumens (nominal), 90 CRI minimum, 3000K CCT, 120V 60Hz, LE and TE phase, matte white flange cut 10 percent dimming, Compliant in all states except California
Product Type	HLS, 9IN, 1200LM, 3000K, Motion Sensor
Special Features	Sizes include 4", 6", & 9"

Manufacturer Information

Brand	HALO
GTIN	00080083256969
Manufacturers Part Number	HLSMS9129301EWH
UPC	080083256969

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLS Round LED Surface Mount



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight Per each	1.26

Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
standard	Energy Star;IECC Compliant;UL Listed;Title 24 Compliant;RoHS Compliant