



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HMJ Holder W/ Sfe-20 Fuse - 20A - 14 Gauge

*Bussmann Fuses*

|                  |                             |
|------------------|-----------------------------|
| Catalog Number   | HMJ                         |
| Manufacturer     | Bussmann Fuses              |
| Description      | 20AMP 32V In Line Fuse HLDR |
| Weight per unit  | 0.0440 (lbs/each)           |
| Product Category | Fuseholders & Fuseblks      |

### Features

|                 |                       |
|-----------------|-----------------------|
| amperage rating | 20 Amp                |
| connection      | 14 AWG 8 In Lead Wire |
| Voltage Rating  | 32 VAC                |

### Dimensions and Weight

|      |                                   |
|------|-----------------------------------|
| Size | 0.69 In Diameter X 2.19 In Length |
|------|-----------------------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | HOLDER W/ SFE-20 FUSE - 20A - 14 GAUGE                                     |
| extra long description | BUSS HMJ HOLDER W/ SFE-20 FUSE - 20  |
| Long Description       | 20AMP 32V IN LINE FUSE HLDR  |
| Product Type           | Holder W/ Sfe-20 Fuse - 20A - 14 Gauge                                     |
| Special Features       | Bayonet Type Knob, For Used With Type SFE and 1/4 In X Various Length Fuse |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00051712719469 |
| UPC   | 051712719469   |

### Taxonomies, Classifications, and Categories

|                      |                          |
|----------------------|--------------------------|
| Category Description | FUSE BLOCKS,FUSE HOLDERS |
| Type                 | IN LINE                  |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 10    |
| Weight Per each | 0.044 |

### Uses, Certifications, and Standards

|                       |           |
|-----------------------|-----------|
| Operating Temperature | 140 Deg C |
|-----------------------|-----------|