



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HR100DX38 100W ED23.5 Mercury Vapor White Mogul Base Lamp

*Ge By Current Lamps*

Catalog Number	HR100DX38
Manufacturer	Ge By Current Lamps
Description	Ge Mercury ED23.5
Weight per unit	0.3800 (lbs/each)
Product Category	Hid Mercury Vapor Lamps

### Features

average life	20000
Base	E39
lumens	4000
Wattage	100

### Material, Color, and Finish

Color	Delux white
color rendering index (cri)	50.0
color temperature	3900
Finish	Delux white
Style	Open or enclosed fixtures

### Descriptions

Description	100W ED23.5 MERCURY VAPOR WHITE MOGUL BASE LAMP
extra long description	GEL HR100DX38 22575 MERCURY
Long Description	GE Mercury ED23.5
Product Type	22575 Mercury
Special Features	7.5IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168225755
Manufacturers Part Number	HR100DX38
UPC	043168225755

### Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
----------------------	---------------

### Packaging

Carton	1
Package	12
Weight Per each	0.38

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------