



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HR100DX38 100W ED23.5 Mercury Vapor White Mogul Base Lamp

Ge By Current Lamps

| | |
|------------------|-------------------------|
| Catalog Number | HR100DX38 |
| Manufacturer | Ge By Current Lamps |
| Description | Ge Mercury ED23.5 |
| Weight per unit | 0.3800 (lbs/each) |
| Product Category | Hid Mercury Vapor Lamps |

Features

| | |
|--------------|-------|
| average life | 20000 |
| Base | E39 |
| lumens | 4000 |
| Wattage | 100 |

Material, Color, and Finish

| | |
|-----------------------------|---------------------------|
| Color | Delux white |
| color rendering index (cri) | 50.0 |
| color temperature | 3900 |
| Finish | Delux white |
| Style | Open or enclosed fixtures |

Descriptions

| | |
|------------------------|---|
| Description | 100W ED23.5 MERCURY VAPOR WHITE MOGUL BASE LAMP |
| extra long description | GEL HR100DX38 22575 MERCURY |
| Long Description | GE Mercury ED23.5 |
| Product Type | 22575 Mercury |
| Special Features | 7.5IN Length |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168225755 |
| Manufacturers Part Number | HR100DX38 |
| UPC | 043168225755 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | MERCURY VAPOR |
|----------------------|---------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.38 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|