



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HR175DX39 175W ED28 Mercury Vapor White Mogul Base Lamp

Ge By Current Lamps

Catalog Number	HR175DX39
Manufacturer	Ge By Current Lamps
Description	Hid Mercury Vapor Lamp, 50, 3900 K, 7800 LM Brightness (Lumens), 175 W, 318 V, White, Hard Glass Material, 20000 H Average Life, Mogul Screw Base, H39 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Length, 30.3 % Mercury Content, 0.53 LB
Weight per unit	0.5300 (lbs/each)
Product Category	Hid Mercury Vapor Lamps

Features

Base	E39
lumens	7800
Wattage	175

Material, Color, and Finish

Color	Delux white
color rendering index (cri)	50.0
Style	Open or enclosed fixtures

Descriptions

Description	175W ED28 MERCURY VAPOR WHITE MOGUL BASE LAMP
extra long description	GEL HR175DX39 24062 MERCURY
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168240628
UPC	043168240628

Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
----------------------	---------------

Packaging

Carton	1
Package	12
Weight Per each	0.53

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------